

# Part numbers

## Molded Case Circuit Breakers

### Tmax T5 300 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I<sub>u</sub> (40°C) = 300 A - Front terminals (F)

Thermal-Magnetic trip unit - TMA - 600V AC / 600V DC	Nominal current		Part number				
	In	I <sub>g</sub>	N (18kA)	S (25kA)	H (35kA)	L (65kA)	V (100kA)
TMA	300 A (210...300 A)	3000 A (1500...3000 A)	T5N300TW	T5S300TW	T5H300TW	T5L300TW	T5V300TW

### Tmax T5 300 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I<sub>u</sub> (40°C) = 300 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current		Part number				
	In		N (18kA)	S (25kA)	H (35kA)	L (65kA)	V (100kA)
PR221DS-LS/I	300 A (120...300 A)		T5N300BW	T5S300BW	T5H300BW	T5L300BW	T5V300BW
PR222DS-LSI	300 A (120...300 A)		T5N300CW	T5S300CW	T5H300CW	T5L300CW	T5V300CW
PR222DS-LSIG	300 A (120...300 A)		T5N300EW	T5S300EW	T5H300EW	T5L300EW	T5V300EW

### Tmax T5 400 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I<sub>u</sub> (40°C) = 400 A - Front terminals (F)

Thermal-Magnetic trip unit - TMA - 600V AC / 600V DC	Nominal current		Part number				
	In	I <sub>g</sub>	N (18kA)	S (25kA)	H (35kA)	L (65kA)	V (100kA)
TMA	400 A (280...400 A)	4000 A (2000...4000 A)	T5N400TW	T5S400TW	T5H400TW	T5L400TW	T5V400TW

### Tmax T5 400 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I<sub>u</sub> (40°C) = 400 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current		Part number				
	In		N (18kA)	S (25kA)	H (35kA)	L (65kA)	V (100kA)
PR221DS-LS/I	400 A (160...400 A)		T5N400BW	T5S400BW	T5H400BW	T5L400BW	T5V400BW
PR222DS-LSI	400 A (160...400 A)		T5N400CW	T5S400CW	T5H400CW	T5L400CW	T5V400CW
PR222DS-LSIG	400 A (160...400 A)		T5N400EW	T5S400EW	T5H400EW	T5L400EW	T5V400EW

### Tmax T5 600 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I<sub>u</sub> (40°C) = 600 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current		Part number				
	In		N (18kA)	S (25kA)	H (35kA)	L (65kA)	V (100kA)
PR221DS-LS/I	600 A (240...600 A)		T5N600BW	T5S600BW	T5H600BW	T5L600BW	T5V600BW
PR222DS-LSI	600 A (240...600 A)		T5N600CW	T5S600CW	T5H600CW	T5L600CW	T5V600CW
PR222DS-LSIG	600 A (240...600 A)		T5N600EW	T5S600EW	T5H600EW	T5L600EW	T5V600EW