

ILPH 232/422-485

ABB contact for Canada [Print to Pdf..](#)

General Information

Extended Product Type:	ILPH 232/422-485
Product ID:	1SNA684233R2700
EAN:	3472596842338
Catalog Description:	ILPH 232/422-485 Serial data converter
Long Description:	ILPH RS232/RS485-422, 24VDC In/out isolated data converter



Categories

Products » Low Voltage Products and Systems » Control Products » Signal Converters » Serial Data Converters

Ordering

EAN:	3472596842338
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85176200

Dimensions

Product Net Width:	22.5 mm
Product Net Height:	100.0 mm
Product Net Depth:	88.0 mm
Product Net Weight:	0.100 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	80.0 mm
Package Level 1 Height:	52.0 mm
Package Level 1 Length:	134.0 mm
Package Level 1 Gross Weight:	0.122 kg

Environmental

Ambient Air Temperature:	Operation 0 ... +50 °C Storage -25 ... +80 °C
---------------------------------	--

Additional Information

Communication Speed:	< = 19.2 kBd
Configuration Type:	Internal jumper configuration
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Power Supply:	24 V
Product Main Type:	ILPH RS232/RS485-422 ISOLE
Product Name:	Serial Data Converters
Rated Control Supply Voltage (U_s):	8.5 ... 28 V DC

Serial Port 1 Type: RS232
Serial Port 2 Type: RS422-RS485
Technical Information: CONVERTER,SIGNAL DATA

Classifications

ETIM 4.0: EC000310 - Interface converter
ETIM 5.0: EC000310 - Interface converter
Object Classification Code: T
UNSPSC: 43172000
