

MSMN

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	MSMN
Product ID:	1SAM101923R0002
EAN:	4013614405334
Catalog Description:	MSMN Driver
Long Description:	MSMN Driver w. screw for manual motor starters, 6x6



Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

Ordering

EAN:	4013614405334
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085

Container Information

Package Level 1 Width:	0.0 mm
Package Level 1 Length:	0.0 mm
Package Level 1 Height:	0.0 mm
Package Level 1 Gross Weight:	0.002 kg
Package Level 1 Units:	1 piece
Package Level 2 Width:	0.0 mm
Package Level 2 Length:	0.0 mm
Package Level 2 Height:	0.0 mm
Package Level 2 Gross Weight:	0.000 kg
Package Level 2 EAN:	4013614409813
Package Level 2 Units:	10 piece

Dimensions

Product Net Width:	0.0 mm
Product Net Height:	0.0 mm
Product Net Depth:	0.0 mm
Product Net Weight:	0.002 kg

Technical

Shaft Diameter:	6x6 mm
Tightening Torque:	0.12 N·m
Product Name:	Driver
Suitable For:	MS116 MS132 MS325 MO325
Suitable for Product Class:	Manual Motor Starters

Environmental

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Tightening Torque UL/CSA: 1.06 in·lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: NoDecNee

Classifications

eClass: 7.0 27379201

E-nummer: 3112084

UNSPSC: 39120000
