

Part numbers

Molded Case Circuit Breakers

Tmax T6 600 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I_u (40°C) = 600 A - Front terminals (F)

Thermal-Magnetic trip unit - TMA - 600V AC / 600V DC	Nominal current		Part number			
	In	I _g	N (20kA)	S (25kA)	H (35kA)	L (42kA)
TMA	600 A (420...600 A)	6000 A (3000...6000 A)	T6N600TW	T6S600TW	T6H600TW	T6L600TW

Tmax T6 600 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I_u (40°C) = 600 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current		Part number			
	In		N (20kA)	S (25kA)	H (35kA)	L (42kA)
PR221DS-LS/I	600 A (240...600 A)		T6N600BW	T6S600BW	T6H600BW	T6L600BW
PR222DS-LSI	600 A (240...600 A)		T6N600CW	T6S600CW	T6H600CW	T6L600CW
PR222DS-LSIG	600 A (240...600 A)		T6N600EW	T6S600EW	T6H600EW	T6L600EW

7

Tmax T6 800 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I_u (40°C) = 800 A - Front terminals (F)

Thermal-Magnetic trip unit - TMA - 600V AC / 600V DC	Nominal current		Part number			
	In	I _g	N (20kA)	S (25kA)	H (35kA)	L (42kA)
TMA	800 A (560...800 A)	8000 A (4000...8000 A)	T6N800TW	T6S800TW	T6H800TW	T6L800TW

Tmax T6 800 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

I_u (40°C) = 800 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current		Part number			
	In		N (20kA)	S (25kA)	H (35kA)	L (42kA)
PR221DS-LS/I	800 A (320...800 A)		T6N800BW	T6S800BW	T6H800BW	T6L800BW
PR222DS-LSI	800 A (320...800 A)		T6N800CW	T6S800CW	T6H800CW	T6L800CW
PR222DS-LSIG	800 A (320...800 A)		T6N800EW	T6S800EW	T6H800EW	T6L800EW