

PS1-4-1-65

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	PS1-4-1-65
Product ID:	1SAM201906R1114
EAN:	4013614400742
Catalog Description:	PS1-4-1-65 3-Phase Busbar
Long Description:	PS1-4-1-65 3-phase busbar for 4 MS116 / MS132 with 1 HK/SK, Ie=65A



Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

Ordering

EAN:	4013614400742
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085

Container Information

Package Level 1 Width:	80.0 mm
Package Level 1 Length:	264.0 mm
Package Level 1 Height:	46.0 mm
Package Level 1 Gross Weight:	0.920 kg
Package Level 1 EAN:	4013614488122
Package Level 1 Units:	10 piece

Dimensions

Product Net Width:	203.5 mm
Product Net Height:	32.3 mm
Product Net Depth:	13.0 mm
Product Net Weight:	0.087 kg

Technical

Rated Operational Voltage:	690 V
Rated Operational Current (I_o):	65 A
Degree of Protection:	IP20
Standards:	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1
Product Name:	3-Phase Busbar
Suitable For:	MS116 MS132
Suitable for Product Class:	Manual Motor Starters

Environmental

Ambient Air Temperature:	Operation -25 +70 °C Storage -50 ...+80 °C
---------------------------------	--

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage UL/CSA: Main Circuit 600 V

Ampere Rating UL/CSA: 65 A

Certificates and Declarations (Document Number)

cUL Certificate: 1SAA963001-1701

Declaration of Conformity - CE: 1SAD938509-0056

GOST Certificate: 1SAA937000-2703

RoHS Information: 1SAA963003-4402

UL Certificate: 1SAA963001-1602

Classifications

E-nummer: 3111681

Object Classification Code: W

UNSPSC: 39121100
