



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Decorator Duplex Receptacle

TR1107GY-BOX

UPC:032664665127

### Dimensions:

- **Height:** 3.81 IN
- **Length:** 1.3 IN
- **Width:** .69 IN

**Warranties:** No Data

### Specifications:

- **Type:** Duplex
- **Allowable Wire Size:** #14 to 10 AWG
- **Amperage Rating:** 15A
- **Mounting Type:** Flush
- **Voltage Rating:** 125V
- **Wiring Method:** Side and push
- **Color:** Gray
- **Contact Material:** Brass
- **Design Type:** Receptacle
- **Nema Configuration:** 5-15R
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Receptacle Type:** Two-pole, three-wire, grounding
- **Style Type:** Decorator
- **Connection Type:** Screw
- **Material:** Thermoplastic

**Supporting documents:** No Data

### Certifications:

- cULus Listed
- NOM

**Product compliance:** No Data



