



Innovative solutions for fast and convenient charging!

Charging solutions for every device

Eaton's USB chargers offer *fast, convenient and efficient charging* of portable electronic devices directly from a standard outlet without bulky adapters or powered computers. This innovative line eliminates clutter in residential and commercial environments while enabling compatibility with USB Type A and C electronics, including smart phones, tablets, e-readers, cameras, MP3 players and more.

Perfect for use in residential, commercial and healthcare applications

- Homes
- Offices
- Hotels
- Classrooms
- Lobbies
- Lounges and coffee houses
- OEM applications
- Airports
- Auditoriums
- Libraries

Eaton's high powered charging solutions



TR
TAMPER RESISTANT

USB-C charging devices

USB-C duplex receptacle offers fast, convenient and efficient charging of Type C devices

- Dual **5A** Type-C charging capacity
- Reversible ports allow for consistent charging regardless of plug-in orientation
- Available in 15A & 20A



TR
TAMPER RESISTANT

USB-A/C charging devices

Quick and easy access for both USB charging and electrical outlets

- Combination devices offering USB Type-A and Type-C ports
- **5A** charging capacity on USB duplex receptacles
- Available in 15A & 20A



TR
TAMPER RESISTANT

USB-A charging devices

Quick and easy access for both USB charging and electrical outlets

- Dual **5A** Type-A charging capacity
- Available in 15A & 20A



USB high power charging devices



TRUSBAC15



TRUSBAC20



TRUSBC15



TRUSBC20



TRUSB5A15



TRUSB5A20

Product description

2-pole, 3-wire grounding
 15A, 125V/AC, 5V/DC, 5.0A
 20A, 125V/AC, 5V/DC, 5.0A
 NEMA 5-15R, 5-20R

Design features

- Standard duplex receptacle with one USB-A and C, or two USB-A or two USB-C or one ports rated at a combined 5.0A
- Dual USB-C charging ports charge most electronic devices that comply with the latest USB-C standard
- Tamper resistant shutters provide compliance with 2017 NEC® Article 406.12 that states that all 15A and 20A, 125V receptacles installed in dwelling units must be tamper resistant
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper is used
- Thermoplastic top and back-body are virtually unbreakable to deliver years of durable performance
- Steel mounting strap is zinc plated for added corrosion resistance
- Convenient patented built-in wire strippers speed installation
- Triple wipe blade contacts and double wipe ground contacts to insure long-term blade retention
- Replaces a standard duplex receptacle



USB chargers with TR duplex receptacle



Rating A	V/AC	USB Rating		Description	Color suffix	Catalog no.
		A	V/DC			
15	125	5.0	5	USB A/C charger with TR duplex receptacle	B, BK, GY, LA, V, W	<input type="checkbox"/> TRUSBAC15__
20	125	5.0	5	USB A/C charger with TR duplex receptacle	B, BK, GY, LA, V, W	<input type="checkbox"/> TRUSBAC20__
15	125	5.0	5	USB C charger with TR duplex receptacle	B, BK, GY, LA, V, W	<input type="checkbox"/> TRUSBC15__
20	125	5.0	5	USB C charger with TR duplex receptacle	B, BK, GY, LA, V, W	<input type="checkbox"/> TRUSBC20__
15	125	5.0	5	USB 5A charger with TR duplex receptacle	B, BK, GY, LA, V, W	<input type="checkbox"/> TRUSB5A15__
20	125	5.0	5	USB 5A charger with TR duplex receptacle	B, BK, GY, LA, V, W	<input type="checkbox"/> TRUSB5A20__

cULus Listed UL 498 and UL1310; NOM certified

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

B	BK	GY	LA	V	W
(Brown)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Tamper resistant

USB charging devices



TR7741



TR7755



TR7756



TR8355



7750

Product description

2-pole, 3-wire grounding
 15A, 125V/AC, 5V DC 2.4A
 15A, 125V/AC, 5V DC 3.1A; 20A, 125V/AC, 5V DC 3.1A
 NEMA 5-15R, 5-20R

5V/DC, 5.0A Total (USB charging station)

Design features

- Standard AC receptacle with two USB charging ports for conveniently charging most electronic components
- USB-A charging ports rated at 5.0 Amps total - 2.5A top two ports, 2.5A bottom two ports (7750 only)
- Dual USB-A charging ports charge most compatible electronic devices with 3.1A total amps
- Tamper resistant receptacles provide compliance with 2014 NEC® Article 406.12 which states that all 15A and 20A, 125V/AC receptacles installed in dwelling units must be tamper resistant
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where jumper is used
- Thermoplastic top and back-body are virtually unbreakable to deliver years of durable performance
- Triple wipe blade contacts and double wipe ground contacts to ensure long-term plug retention
- Convenient patented built-in wire strippers speed installation
- Steel mounting strap is zinc plated for added corrosion resistance (7750 only)
- Replaces a standard duplex receptacle and uses a decorator style wallplate



Combination USB charger with TR receptacle



Rating A	V/AC	USB Rating A	V/DC	Description	Color suffix	Catalog no.
15	125	2.4	5	Combination USB charger with TR single receptacle	B, BK, GY, LA, V, W	□ TR7741__
15	125	3.1	5	USB charger with TR duplex receptacle, wire leads	B, BK, GY, LA, RB, SG, V, W	□ TR7755__
20	125	3.1	5	USB charger with TR duplex receptacle, wire leads	B, BK, GY, LA, RB, SG, V, W	□ TR7756__
15	125	3.1	5	USB charger with hospital grade TR duplex receptacle	GY, LA, RD, V, W	□ TR8255__
20	125	3.1	5	USB charger with hospital grade TR duplex receptacle	GY, LA, RD, V, W	□ TR8355__

cULus Listed UL 498 and UL1310; NOM certified

USB charging station



USB Rating A	V/DC	Description	Color suffix	Catalog no.
5.0	5	USB multiport charging station	BK, GY, LA, V, W	□ 7750__

UL Listed to UL1310

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: B (Brown), BK (Black), GY (Gray), LA (Light Almond), RB (Oil Rubbed Bronze), RD (Red), SG (Silver Granite), V (Ivory), W (White)

B	BK	GY	LA	RB	RD	SG	V	W
(Brown)	(Black)	(Gray)	(Lt. Almond)	(Oil Rubbed Bronze)	(Red)	(Silver Granite)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Tamper resistant