

Network Enclosures

Features

- Flush or surface mount enclosure (hardware provided)
- Hinged cover can be mounted to swing from either side
- Integral trim ring hides rough-in hole in sheet rock providing a finished appearance (except NSOBOX48)
- Horizontal and vertical module mounting holes for maximum flexibility
- Unique 89D bracket mounting holes allow easy mounting of 66 blocks and peripherals
- Provisions to mount optional duplex power and lock kit available
- Integral cable management slots and tie-wraps provided to help dress cable runs
- Additional nylon push pins provided to assist module mounting
- Material: 20-18 gauge steel
- Finish: white, powder coat
- cULus Listed 1863

Network Enclosures

Pre-Configured Network System

Description	Catalog Number
Pre-Configured Network System	NSOBNK14
Basic home network kit includes:	
One box with hinged cover NSOBOX14,	
One primary 8-port telephone module NSOPTM8,	
One four way coaxial splitter module NSOVM4	



NSOBOX10

10 Inch Network Enclosure for MDU and Modular Applications

Description	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	No. of Module Placement	Catalog Number
With hinged cover	11.55" (293)	15.65" (398)	4.08" (104)	3	NSOBOX10
With panel cover	11.07" (281)	–	4.08" (104)	3	NSOBOX10BC
10"H box only	10.07" (256)	14.38" (365)	3.96" (101)	3	NSOBOX10B
Hinged door	11.55" (293)	15.65" (398)	0.58" (15)	–	NSOBOX10D
Panel cover	11.07" (281)	15.50" (594)	0.20" (5)	–	NSOBOX10C



NSOBOX14

14 Inch Network Enclosure

With hinged cover	15.55" (395)	15.65" (398)	4.08" (104)	5	NSOBOX14
With panel cover	15.10" (384)	15.54" (395)	4.08" (104)	5	NSOBOX14BC
14"H box only	14.00" (356)	14.38" (365)	3.96" (101)	5	NSOBOX14B
Hinged door	15.55" (395)	15.65" (398)	0.33" (8)	–	NSOBOX14D
Vented door (louver)	15.55" (395)	15.65" (398)	0.52" (15)	–	NSOBOX14DL
Panel cover	15.11" (384)	15.54" (395)	0.20" (5)	–	NSOBOX14C
2"D extension bracket with ventilation and WiFi KOs	15.30" (389)	15.57" (395)	2.00" (51)	–	NSOBOX14X2

28 Inch Network Enclosure

With hinged cover	29.55" (751)	–	–	11	NSOBOX28
With panel cover	29.13" (740)	15.54" (395)	4.08" (104)	11	NSOBOX28BC
28"H box only	28.00" (711)	14.38" (365)	3.96" (101)	11	NSOBOX28B
Hinged door	29.55" (751)	15.65" (398)	0.33" (8)	–	NSOBOX28D
Vented door* (louver)	29.55" (751)	15.65" (398)	0.52" (15)	–	NSOBOX28DL
Panel cover	29.29" (744)	15.54" (395)	0.20" (5)	–	NSOBOX28C
2"D extension bracket with ventilation and WiFi KOs	29.3" (744)	15.57" (395)	2.00" (51)	–	NSOBOX28X2



NSOBOX28

48 Inch Network Enclosure

With hinged cover	48.94" (1243)	14.94" (379)	4.07" (103)	21	NSOBOX48*
Trim ring					NSOBOX48R

Note: *Door covers rough-in, no trim ring provided.