## **SIEMENS**

Data sheet US2:QE260



Siemens Low Voltage Residential Circuit Breakers Miniature Circuit Breakers GFCI - Equipment Protect 2-pole plug-on 10k are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Sub Brand: N/A Type: QE Special Features: N/A Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240 V Amperage Rating: 60A Load Rating: N/A Frequency Rating: N/A Phase: N/A Frame: N/A Trip Type: N/A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 2P

Number of poles	2
Suitability for operation	Electrical Distribution
Electricity	
Continuous current rated value	60 A
Model	
Product brand name	SIEMENS
Type of electrical connection	PLUG-IN
Mechanical Design	
Depth [in]	3 in
Design of the product	QE
Height [in]	6 in
Width [in]	4 in
General product approval	
Standard	UL 489
last modified:	05/28/2019