

# 

LED Switchable Lumen Flat Panel

4 2


## 3-in-1 Panel for Everyday Ease

TIL

CPANL from Lithonia Lighting® offers the ultimate in mounting flexibility and lumen options. The integrated driver and rigid, deep-drawn housing allow this low-profile panel to suspend, mount directly to the surface, or integrate in a standard T-grid ceiling. CPANL is the solution when traditional panels with external drivers are incompatible. The Switchable Lumen feature adds to the versatility of CPANL, providing three panel solutions in one. CPANL is suitable for both new construction and renovation for applications such as schools, commercial office, retail and healthcare applications.

#### **Features and Benefits:**

- Expanded lumen range supports a variety of tasks and mounting heights
- Switchable Lumen feature provides flexibility to adjust lumens right on the jobsite
- Ultra-thin and deep-drawn housing design enables surface flush, surface box, suspension and recessed mounting options
- Integrated driver capable of 10% dimming and 120-277v operation
- High-performance LEDs provide more than 60,000 hours of reliable illumination
- Available in 1x4, 2x4 and 2x2 configurations to suit your application needs




### **CPANL<sup>™</sup> LED Flat Panel**



See CPANL specification sheet for full list of compatible accessories.

#### Robust Construction and Mounting Versatility

CPANL is precision-engineered with an integrated driver for unrestricted mounting opportunities. The deep-drawn backplate offers superior rigidity, making it perfect for suspended applications without bowing or warping. CPANL can also be mounted directly to a surface for a modern, streamlined look.





- Switchable Lumen feature: Easily adjust lumens by using the three position switch located on the back of the CPANL to create the right amount of illumination in a space. This benefits both the contractor and the distributor by reducing the number of SKUs needed.
- The ultra-thin, integrated driver design of the CPANL allows up to 50 percent more panels to fit on a truck or lift versus external driver alternatives, saving you time and money.
- Direct surface mounting using the optional H-bracket leaves both hands available for wiring, making a single-person install simple to achieve.
- Our most popular CPANL configurations are part of the Contractor Select<sup>™</sup> program to make your stock selection process easy and ensure quick delivery to support your business.

CI Code	Description	Lumen Range	Wattage	Contractor Select <sup>™</sup>
*250CSL	CPANL 2X4 40/50/60LM 35K M2	4000/5000/6000	32/42/52	CS
*250CXS	CPANL 2X4 40/50/60LM 40K M2	4000/5000/6000	32/42/52	CS
*250E3S	CPANL 2X4 40/50/60LM 50K M2	4000/5000/6000	32/42/52	
*250E4S	CPANL 2X2 24/33/44LM 35K M4	2400/3300/4400	20/28/39	CS
*250E5S	CPANL 2X2 24/33/44LM 40K M4	2400/3300/4400	20/28/39	CS
*250E6S	CPANL 2X2 24/33/44LM 50K M4	2400/3300/4400	20/28/39	
*250EGS	CPANL 1X4 24/33/44LM 35K M4	2400/3300/4400	20/28/39	
*250EKS	CPANL 1X4 24/33/44LM 40K M4	2400/3300/4400	20/28/39	
*250ELS	CPANL 1X4 24/33/44LM 50K M4	2400/3300/4400	20/28/39	

Visit www.lithonia.com for more information

One Lithonia Way, Conyers, GA 30012 | Phone: 800.705.7378 | www.acuitybrands.com © 2019 Acuity Brands Lighting, Inc. All Rights Reserved. | LL\_8760.01\_0719

