

Carlton Weatherproof fittings

Nonmetallic strain-relief multi-bushing fitting



Carlton indoor/outdoor nonmetallic strain-relief fittings are uniquely designed for high-performance reliability. Available for a variety of cables and applications. Carlton fittings make installations easier, faster and more secure... every time.

Features and benefits:

- Highly adaptable for use in indoor/outdoor, residential/commercial applications
 - Light arrays
 - Pools
 - AC/heat pump units
- Flexible elastomer bushings for a snug and secure fit on a variety of cable shapes and sizes
- NMWU cable compatible
- Unique overlapping compression fingers for an extra-strength grip around every bushing
- Hand-/plier-friendly gland nut for optimal ease-of-use
- Temperature rating to 85 °C
- Multiple trapezoidal nut threads for easy turning and added strength



	Cat. no.	Description	Trade size (in.)	Order quantity
	SRC-075	Nonmetallic unthreaded strain relief fitting	¾	25 (min./mult.)



	SRTC-075	Nonmetallic threaded strain relief fitting	¾	25 (min./mult.)
--	----------	--	---	-----------------



	SRTC-050	Nonmetallic threaded strain relief fitting	½	25 (min./mult.)
--	----------	--	---	-----------------



Bushing	NMD 90 cables (Loomex™-Romex™)	NMWU cables	Cord cable diameter range (in.)
	14/3	–	0.240–0.340
	12/3	14/3	0.340–0.450
	10/3	14/3	0.340–0.450
	8/3	12/3	0.450–0.590
	8/3	10/3	0.450–0.590
	14/2	14/2 and 12/2	–
	12/2	14/2 and 12/2	–
	10/2	14/2 and 12/2	–