# Regressed gimbal downlight with thin trim











This versatile modern thin-trim 2-, 4-, and 6-inch gimbal with multi-directional adjustable swivel produces high light output with minimal glare as a result of its regressed light source. Ideal for general lighting or for areas requiring a directional light to showcase unique elements or to create dramatic wall-wash effects.



Model	Size	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
RGM2-3K	2"	8 W	660 lm	800 lm	90	3000 K	120 V
RGM4-3K	Ц"	12 W	1050 lm	1400 lm	90	3000 K	120 V
RGM6-3K	6"	15 W	1270 lm	1700 lm	90	3000 K	120 V

# **Specifications**

Every fixture includes a junction box with integrated dimmable driver
Can be daisy chained
Superior LED performance and lifespan
Regressed light source
Minimal heat emission
Aluminum construction
IC certification (suitable for direct contact with insulation)
Air-tight certified as per ASTM E283-04
Suitable for wet locations

30° tilting, 360° rotation

### Finish

BK BlackSN Satin NickelWH White

### **Accessories**

# **RFP-UNI**

Universal rough-in plate

# Order example

# RGM6-3K-SN

6" gimbal recessed downlight with 1270 Lumens at 3000 K in a satin nickel finish

