


nVent CADDY Cat CM U-Hook, Strut Mount – CAT200CM



- Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic
- Integrated quick-attach T-nut allows U-Hooks to be quickly mounted to strut
- System offers a convenient pathway for wires and cables
- Specially designed U-Hooks have large-diameter, rounded support surfaces
- Rounded edges help prevent over-bending and kinking of cables
- Ideal for retrofit applications where cable runs need to be routed around existing building infrastructure
- Compliant with NEC® and ANSI®/TIA structured cabling systems standards



Part Number	CAT200CM
Material	Steel
Finish	Electrogalvanized
Included Components	Quick-Attach T-Nut
Cable Capacity, Cat 5e	450
Cable Capacity, Cat 6	350
Cable Capacity, Cat 6A	215
A	8"
Area	21 in ²
Hole Size (HS)	3/8"
Static Load (F)	100 lb
Certifications	cULus
Standard Packaging Quantity	10 pc
UPC	78285646486
EAN-13	8711893003116

ANSI is a registered trademark of American National Standards Institute. NEC is a registered trademark of, and National Electrical Code (NEC) standard is a copyright of the National Fire Protection Association, Inc. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

