


nVent CADDY Rod Lock Coupler – CRLC37EG



- Joins two sections of threaded rod by an easy "push-to-install" mechanism
- Can be easily installed at the end of a threaded rod, or to any existing male thread
- Plastic protection cap prevents dirt or structural coatings from obstructing the "push-to-install" mechanism
- Prefabricated assemblies easily lift and lock into place, helping to save time and money
- Works with slightly damaged threads and minor burrs on the threaded rod



Part Number	CRLC37EG
Material	Steel
Finish	Electrogalvanized
Static Load Safety Factor	3.5:1
Rod Size (RS)	3/8"
Height (H)	2.4"
Wrench Size 1	1/2"
Wrench Size 2	15/16"
Static Load (F)	1,000 lb
Standard Packaging Quantity	25 pc
UPC	78285686398

Wrench Size 1 represents hex size used to tighten to threaded rod from structure. Wrench Size 2 represents nVent CADDY Rod Lock hex nut size.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

