

G1 *VERSI*TM TUGGER

Get More Done In A Day

Pulls don't slow down due to fatigue

Works Where You Work

Portable & compatible with most

18V - 20V cordless drills



30% Faster

Setup, Pull & Reset
than manual pulling*



*When setting up & pulling poly line into a 200' run

ORDERING INFORMATION

CAT. NO.	DESCRIPTION
G1	G1 Versi-Tugger™ includes 17" boom, pulling head, capstan, frame & gearbox *Drill NOT included

SPECIFICATIONS

Pull Force	Constant: Up to 600 lbs Peak Force: 1,000 lbs	Conduit Size	1/2" - 4"
Boom Length	8" & 17" Extendable up to 10' with 1' Rigid conduit	Roller Capacity	Up to 7/8" rope
Drill Compatibility	Most 18V - 20V cordless drills	Pulling with Rope	Up to 1/2" rope
Spooling Capacity	Poly Line - 600' Measuring Tape - 1,150' Mule Tape - Up to 100'		

Pulling Products

Check out these additional Greenlee Pulling Products



Pulling Rope

Use up to 1/2" rope with a maximum rated capacity that meets or exceeds the cable pullers maximum pulling force



Poly line

Greenlee poly line comes ready-to-use, with a pre-punched hole in lid & resealable cap. Use with our fish tapes or power fishing systems when you install cable. Available in 6,500' or 500' lengths & 210 lb or 500 lb breaking strength.



Pulling & Measuring Tape

Use Greenlee's durable & stretch-resistant tape to easily install wire in conduit & PVC. The tape is lubricated to reduce burn-through in inner duct & has easy-to-read footage markings for quick & accurate measurements. It is available in various tensile strengths for use in any application.

Fish & measure conduit runs in one operation. Greenlee measuring tape has permanently printed measurements every foot from zero to 3000' IN (914 m) & is made of strong, waterproof polyester.