



Catalog Number	

Notes

Туре

Contractor Select™ **TFX LED** Floodlights

The TFX LED floodlights from Lithonia Lighting deliver the best value in lighting, from a brand you can trust. Superior performance and robust design make this product suitable for any general purpose floodlighting application.

FEATURES:

- Ideal solution to replace up to 400W metal halide floodlights
- Floodlight pays for itself in less than 2 years
- Robust design and cost effective ideal for outdoor installations









Luminaire	сст	Lumens	Input Watts	Finish	Voltage	Catalog Number	CI Code	UPC	Pallet qty.	Replaces Up To
TFX1	4000K	7,300	54W	DARK BRONZE	120-277V	TFX1 LED 40K MVOLT THK DDBXD M6	*2552M5	193047670173	180	150W Metal Halide
	4000K	7,300	54W	DARK BRONZE	120-277V	TFX1 LED 40K MVOLT YK DDBXD M6	*2552M6	193047670180	180	150W Metal Halide
	4000K	7,300	54W	WHITE	120-277V	TFX1 LED 40K MVOLT THK DWHXD M6	*2552M7	193047670197	180	150W Metal Halide
TFX2	4000K	13,200	94W	DARK BRONZE	120-277V	TFX2 LED 40K MVOLT IS DDBXD	*2552MA	193047670241	45	250W Metal Halide
	4000K	13,200	94W	DARK BRONZE	120-277V	TFX2 LED 40K MVOLT YK DDBXD	*2552ME	193047670234	63	250W Metal Halide
	5000K	13,200	94W	DARK BRONZE	120-277V	TFX2 LED 50K MVOLT IS DDBXD	*2581FG	193048041545	45	250W Metal Halide
	5000K	13,200	94W	DARK BRONZE	120-277V	TFX2 LED 50K MVOLT YK DDBXD	*2581FK	193048041552	63	250W Metal Halide
TFX3	4000K	25,600	188W	DARK BRONZE	120-277V	TFX3 LED 40K MVOLT IS DDBXD	*2552MF	193047670265	24	400W Metal Halide
	4000K	25,600	188W	DARK BRONZE	120-277V	TFX3 LED 40K MVOLT YK DDBXD	*255MJ	193047670258	36	400W Metal Halide
TFX4	4000K	41,000	296W	DARK BRONZE	120-277V	TFX4 LED 40K MVOLT IS DDBXD	*2552MM	193047670302	12	1000W Metal Halide
	4000K	41,000	296W	DARK BRONZE	120-277V	TFX4 LED 40K MVOLT YK DDBXD	*2552MN	193047670326	12	1000W Metal Halide

More configurations are available. <u>Click here</u> or visit www.acuitybrands.com and search for TFX LED.

Accessories: Order as separate catalog number.

Click here to visit <u>Accessories</u>.





Specifications

INTENDED USE:

The traditional and robust design of the TFX LED floodlight with energy efficient LEDs, is suitable for replacing up to 400W Metal Halide. It is ideal for landscape, signage, and accent lighting in heavy commercial and residential applications.

CONSTRUCTION:

Die-cast aluminum housing has integral heat sink fins to optimize thermal management through conductive and convective cooling. The LED driver is mounted in direct contact with the casting to promote low operating temperature and long life. Housing is completely sealed against moisture and environmental contaminants (IP66). Low EPA for optimized wind loading.

ELECTRICAL:

Light engine(s) consist of LEDs directly coupled to the housing to maximize heat dissipation and promote long life (up to L90 / 100,000 hrs.).

INSTALLATION:

Integral slipfitter or yoke facilitates quick and easy installation to a variety of mounting accessories.

LISTINGS:

UL certified to U.S. and Canadian standards. Luminaire is IP66 rated. Rated for -40 $^{\circ}\mathrm{C}$ minimum ambient.


DesignLights Consortium® (DLC) Premium qualified product and DLC qualified product. Not all versions of this product may be DLC Premium qualified or DLC qualified. Please check the DLC Qualified Products List at <u>www.designlights.org/QPL</u> to confirm which versions are qualified.

WARRANTY:

5-year limited warranty. Complete warranty terms located at:

www.acuitybrands.com/support/customer-support/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.



TFX3 with Yoke Mount


Dimensions

All dimensions are inches (centimeters) unless otherwise indicated.




TFX2


TFX4









TFX1 with Yoke Mount



TFX2 with Knuckle Mount



TFX2 with Yoke Mount



TFX4 with Knuckle Mount

