



S9415

13PAR30/SN/LED/40'/2700K/120V/D
 13 watt PAR30 Short Neck LED; 2700K; 40' beam spread;
 Medium base; 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- ABS Lens
- Dimmable



S9415

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9415 | 045923094156 | 120 | 13 | 50 | PAR30SN | Medium | E26 |

| Lamp Code | Dimmable/Non-Dimmable | Suggested Dimmers | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours |
|---------------------------------|-----------------------|--|--------|---------------|---------------|----------------|---------------------|
| 13PAR30/SN/LED/40'/2700K/120V/D | Dimmable | Compatible dimmers for S9415 | Silver | 3-5/8" | 3-3/4" | 1000 | 25000 |

| Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | CEC Status |
|-------------|------------|-----|-----------------|------|--------------|-------------|--|
| 2700 | Warm White | 80 | 40 | 12/6 | Box | ENERGY STAR | Non-Compliant Possible sub: S9486 |

| RoHS Compliant | Fixture Type | UL or ETL Listed | UL Classification | Warranty |
|----------------|----------------|------------------|----------------------------|--------------------------------|
| Yes | Enclosed Rated | Yes | cULus - Wet Location Rated | 3 Year Limited |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

