



S39396

100W/LED/HID/5000K/100-277V/EX39
100 watt - LED HID Replacement; 5000K; Mogul extended base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP64 rated
- For outdoor & indoor use
- Base up or base down operation
- High-bay / Low-bay / Post-top
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V
- Built in Surge Protection: 6KV

Shatter resistant materials, acceptable for use in food prep areas



S39396

Minimum Compartment Size		
Length	Width	Depth
9.25 inch	9.25 inch	17.32 inch

Optional Accessories

- In-line surge protector [80-929](#)

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
-------------	--------------	-----	---------------	-------	---------------------	-------------------------	------------------------

S39396	Hi-Pro	045923303968	100 - 277	100	50/60Hz	500W	150W		
HID Equivalent	Base	ANSI Base	Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	
400W	Mogul Extended	EX39	100W/LED/HID/5000K/100-277V/EX39		Non-Dimmable	White	9"	4-23/32"	
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Burning Position	Operating Temperature		
14300	50000	5000	Natural Light	80	300	Up or Down Operation Only	-20C (-4F) to a maximum of +65C (+149F)		
Pack	Package Type	CEC Status	DLC ID:	Material	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	Thermal Management
12	Box	Lawful for sale in California	LPJL30QF2F2 DLC Search	Aluminum	Yes	Yes	cULus - Damp Location Rated	5 Year Limited	More Details About



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

