



S13120

70W/LED/HID/HP360/827K/100-277V
 70W LED HID Replacement; 2700K; Mogul extended base; 100-277V

Features

- Light panels rotate and angle
- Built-in surge protection - 4KV
- IP64 rated
- Direct wire range voltage 100-277V
- Approved for enclosed fixtures



S13120

Minimum Compartment Size		
Length	Width	Height
8 inch	8 inch	10.75 inch

*Dimmable via WiFi accessory [80-954](#) only.

Additional accessories:

- [80-955](#) - Hi-Pro Motion Sensor / PIR
- [80-956](#) - Hi-Pro Photocell
- [80-957](#) - Hi-Pro Motion Sensor / MW

Item Number	UPC	Voltage	Watts	HID Equivalent	Power Factor	Base	ANSI Base
S13120	045923131202	100-277	70	250	0.90	Mogul Extended	EX39

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
70W/LED/HID/HP360/827K/100-277V	Dimmable*	White	11-13/16"	7.00"	10450	50000	2700

Color	CRI	Beam Spread Deg	Burning Position	Operating Temperature	Pack	Package Type	CEC Status
Warm White	80+	360	Universal	Enclosed fixture -30C (-22F) to a maximum of +45C (+113F); Open fixture -29C (-20.2F) to a maximum of +60C (140F)	8/1	Box	Lawful for sale in California

RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty
Yes	Enclosed Rated Lamp	Yes	cULus Classified - Damp Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

