



Representative

Catalog Number: 54112 UB
Product ID: 7TAH007970R0323
UPC Number: 78621086963
Status: A

Copper One-Hole Lug, 90 Degree Bend Standard Barrel, Peep Hole, Max 35kV, Wire Size 4/0 AWG, 3/8 Inch Bolt Size, 3/8 Inch Hole Spacing, Tin Plated, Die Code 54, Die Color Code Purple 54

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel 90 Degree Bend
Standard	UL E9809
Cable Size	4/0 AWG
Stud Size	3/8 in
Number Of Holes	1
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Purple

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	90°
Slender flange model	N
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	5
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	50
Outer Dimensions (inches)	12.3x6.3x4
Weight Uom	9.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001111
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com