

## Eaton, 22.5 mm RMQ-Titan Pushbutton

**M22-D-R-K10**

**UPC:**786685276212

### **Dimensions:**

- **Height:** 2.16 IN
- **Length:** 1.46 IN
- **Width:** 1.18 IN

**Weight:**.051 LB

### **Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### **Specifications:**

- **Type:** Pushbutton
- **Action:** Momentary
- **Actuator:** Button, Flush
- **Actuator Color:** Red
- **Bezel:** Silver
- **Contact Configuration:** 1NO
- **Enclosure:** IP67, IP69K
- **Environmental Rating:** IP67, IP69K, NEMA 4X, 13
- **Illumination:** Non-illuminated
- **Mounting:** Flush
- **Nema Rating:** NEMA 4X, 13
- **Operating Cycles:** 5,000,000 operations
- **Size:** 22.5 mm
- **Product Category:** Flush pushbutton
- **Series:** M22

### **Supporting documents:**

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22 Operators and Accessories](#)



- [M22 Pilot Devices](#)
- [Eaton Specification Sheet - M22-D-R-K10](#)

**Certifications:**

- CCC Marked
- CSA Certified
- Lloyd's Register Certified

**Product compliance:**

- Bureau Veritas
- CE Marked
- GoST-R