
8 PORT CAT6 NETWORK INTERFACE MODULE

AC1068 | [On-Q](#)

FEATURES & BENEFITS

The AC1068 module is designed to connect your Router / Switch to wired networking locations throughout the home. Eight front-mounted 110-1DC punchdown terminals and RJ-45 connectors allow for easy configuration of the home network with patch panel simplicity. The network interface module is UL listed and exceeds TIA/EIA 568-C.2 industry standards.



- Supports punchdown termination of up to 8 Cat6 data lines for easy interface with the home network
- Provides connectivity for ethernet connected devices like computers, TV's, gaming systems and network streaming devices
- Easy access to front mounted 110-1DC Punchdown terminals and RJ45 Jacks
- Module mounts in all On-Q structured wiring enclosures
- Supports termination using T568A wiring standard, is UL listed and exceeds TIA/EIA 568-C.2 industry standards

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat 6
Color: Black/Yellow
Number Of Ports: 8
Performance Category: Cat6
Termination: 110 IDC Punchdown / RJ45 Connectors - T568A Wiring

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UL Standard: CAN/CSA C22.2 No. 182.4, Plugs, Receptacles and Connectors for Communication Systems; UL 1863, Communications-Circuit Accessories

CONSTRUCTION INFORMATION

Material 4: Metal Bracket with Printed Circuit Board
Installation Location: On-Q Enclosure (Metal & Plastic)

DIMENSIONS

Depth (Metric): 38.1mm
Depth (US): 1.5"
Height (Metric): 161.9mm
Height (US): 6.41"
Width (Metric): 69.9mm
Width (US): 2.9"
Overall Dimensions (Metric): 161.9mm H x 69.9mm W x 38.1mm D
Overall Dimensions (US): 6.41" H x 2.9" W x 1.5" D
Primary Packaging Weight (Metric): 0.200kg
Product Weight (US): 0.363lbs

TECHNICAL INFORMATION

Mounting: Tabs / Plungers & Grommets
Operating Temperature (Celsius): 0°C - 50°C
Supported Standards: TIA/EIA 568-C.2