

Project Name

Location

Prepared By



SATCO S29390

18W/LED/HID/5000K/100-277V E26

Notes

[www] 11-02-2020 01:57:05

General

| | |
|-------------------------|---|
| Status | Discontinued |
| Substitute | S39390 |
| Watts | 18 |
| Incandescent Equivalent | 120 |
| Fluorescent Equivalent | 32 |
| HID Equivalent | 70 |
| Volts | 100V-277V |
| Shape | Comcob |
| Base | Medium |
| ANSI Base | E26 |
| CCT (Kelvin) | 5000 |
| Temperature | Natural Light |
| CRI | 80+ |
| Lumens | 2700 |
| Beam Spread | 300 |
| Dimmable | Non-Dimmable |
| Hours Rated | 50000 |
| Lamp Type | Comcob |
| Technology | LED |
| Min Compartment Size | Length: 8.5 in. Width: 6 in. Depth: 6 in. |
| Ballasting Requirements | Ballast Bypass-Direct wire only 100-277V |

Electrical

| | |
|-----------------------|---|
| Working Voltage | AC 90-305V |
| Operating Frequency | 50/60 Hz |
| Power Factor | >.9 |
| Burning Position | Universal |
| Operating Temperature | -20C (-4F) to a maximum of +40C (+104F) |

Physical

| | |
|--------------|------|
| MOL | 6.78 |
| MOD | 2.75 |
| Weight (lb.) | 0.86 |

Additional Information

| | |
|----------------------------|--|
| Additional Info | Replaces HID, CFL, and Incandescent; UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg) |
| Rated For Enclosed Fixture | Yes |
| IP Rating | IP65 |
| Warranty | 5 Year Limited - Hi-Pro |

Compliance

| | |
|-----------------|-------|
| Safety Listing | cULus |
| Location Rating | Damp |
| Energy Star | No |

| | |
|----------------|-------------------------------|
| DLC Approved | No |
| CEC Status | Lawful for sale in California |
| RoHS Compliant | Yes |
| SDS Sheet | LED_Lamp |

