

Project Name

Location

Prepared By



SATCO S29392

36W/LED/HID/5000K/100-277V E26

Notes

[www] 11-09-2020 01:10:23

General

Status	Discontinued
Substitute	S39392
Watts	36
Incandescent Equivalent	200
Fluorescent Equivalent	55
HID Equivalent	150
Volts	100V-277V
Shape	Corncob
Base	Medium
ANSI Base	E26
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80+
Lumens	4800
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Min Compartment Size	Length: 17.3 in. Width: 9.25 in. Depth: 9.25 in.
Ballasting Requirements	Ballast Bypass-Direct wire only 100-277V

Electrical

Working Voltage	AC 90-305V
Operating Frequency	50/60 Hz
Power Factor	>.9
Burning Position	Universal
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)

Physical

MOL	9.16
MOD	3.66
Housing Color	White
Weight (lb.)	1.68

Additional Information

Additional Info	Replaces HID, CFL, and Incandescent; UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus
Location Rating	Wet

Energy Star	No
DLC Approved	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp

