

Project Name

Location

Prepared By



SATCO S29394

54W/LED/HID/5K/100-277V/EX39

Notes

[www] 11-09-2020 01:10:23

General

Status	Discontinued
Substitute	S39394
Watts	54
Incandescent Equivalent	300
Fluorescent Equivalent	85
HID Equivalent	250
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80+
Lumens	7200
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Min Compartment Size	Length: 17.3 in. Width: 9.25 in. Depth: 9.25 in.
Ballasting Requirements	Ballast Bypass-Direct wire only 100-277V

Electrical

Working Voltage	AC 90-305V
Operating Frequency	50/60 Hz
Power Factor	0.9
Burning Position	Up or Down Operation Only
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)

Physical

MOL	10.75
MOD	3.69
Weight (lb.)	2.15

Additional Information

Additional Info	Classified under UL 1598C; Replaces HID, CFL, and Incandescent; UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP65
Shatter-Proof Type	Shatter resistant materials. Acceptable for use in food prep areas
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	PLGVDTP7L3LM
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp

