

Project Name

Location

Prepared By



SATCO S29910

25T5/LED/46-840/DR

Notes

[www] 11-09-2020 01:16:23

General

Status	Active
Watts	25
Fluorescent Equivalent	54
Ballast Type	Type A
Shape	T5
Base	Miniature Bi Pin
ANSI Base	G5
Nominal Length	48
Finish	Gloss
CCT (Kelvin)	4000
Temperature	Cool White
CRI	82
Lumens	3500
Beam Spread	185
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast required
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	48
MOD	0.63

Additional Information

Includes	Integrated thermal fuse at pins
Integrated Features	Integrated thermal fuse at pins
Warranty	5 Year Limited - T5 LED Bulbs

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLYBR7TV2C9K
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
NSF Approved	Yes - Approved