

D7 Series General Purpose Plug-In Relay

D7PF4AA

UPC:782116484973

Dimensions:

- **Height:** 1.1 IN
- **Length:** 1.54 IN
- **Width:** 1.6 IN

Weight: .15 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 120V
- **Contact Configuration:** 4PDT
- **Contact Material:** Silver alloy
- **Contact Rating:** 15A
- **Cover:** Full featured
- **Enclosure:** IP40
- **Maximum Voltage:** 300V switching
- **Options:** LED test button, flag indicator, lock-down door, finger-grip cover, ID tag
- **Resistance:** 2220 Ohms
- **Series:** D7 series
- **Terminals:** Plug-in

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [D7_F4 3D Model Xchange](#)
- [D7_F4 AutoCAD 2D Footprint \(mm\)](#)
- [D7_F4 2D Drawing Xchange](#)
- [D7_F4 3D Inventor](#)
- [D7_F4 2D PDF](#)



- [D7_F4 AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - D7PF4AA](#)

Certifications:

- CSA file No. LR217069
- UL Listed file E65657
- CSA file No. LR217017
- cRUus
- UL Listed file E37317

Product compliance:

- RoHS Compliant
- CE Marked