# **Eaton PowerXL DG1 variable frequency drive**

DG1-35041FN-C21C

UPC:786685975276

#### **Dimensions:**

Height: 28 INLength: 17 INWidth: 15 IN

Weight:92 LB

Warranties: No Data

## **Specifications:**

Brake Chopper: No brake chopper
Display: LCD (graphical) display
Output Current: 41 A, 30 kW
Enclosure: IP21/Type 1 enclosure

Horsepower: 40 hpPhase: Three-phase

• Protection Filtering: Internal EMC filter and

DC choke

• Series: DG1 Series

• Special Features: Coated boards

Voltage Rating: 575 ∨

### **Supporting documents:**

• Product Datasheet - DG1-35041FN-C21C

 Eaton Specification Sheet - DG1-35041FN-C21C

#### **Certifications:**

- cUL Listed
- UL Listed

### **Product compliance:**

- CE Marked
- RoHS Compliant
- C-Tick Compliant

\_\_\_\_\_

© 2016 Eaton. All rights reserved.