



S9420

13PAR30/SN/LED/60/2700K/120V/D
 13 watt PAR30 Short Neck LED; 2700K; 60° beam spread;
 Medium base; 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- ABS Lens
- Dimmable



S9420

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9420	045923094200	120	13	50	PAR30SN	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
13PAR30/SN/LED/60/2700K/120V/D	Dimmable	Compatible dimmers for S9420	Silver	3-5/8"	3-3/4"	1000	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	CEC Status
2700	Warm White	80	60	12/6	Box	ENERGY STAR	Non-Compliant Possible sub: S9486

RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty
Yes	Enclosed Rated	Yes	cULus - Wet Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

