

Project Name

Location

Prepared By



SATCO S29558

9.5A19/LED/40K/ND/120V/4PK

Notes

[www] 11-09-2020 01:10:23

General

Status	Active
Watts	9.5
Incandescent Equivalent	60
Fluorescent Equivalent	13
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	4000
Temperature	Cool White
CRI	84
Lumens	800
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Power Factor	0.6
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	4.31
MOD	2.38

Additional Information

Additional Info	Solid State LED lighting
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2318798
CEC Status	Non-Compliant
CEC Compliant Substitute	S8562
RoHS Compliant	Yes
SDS Sheet	LED_Lamp