## SATCO NUVO

Project Name

Location Prepared By



Notes	

Status	Active
Watts	9.5
Incandescent Equivalent	60
Fluorescent Equivalent	13
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	83
Lumens	800
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED
Electrical	
Power Factor	0.6
Operating Temperature	-25C (-13F) to a maximum of +45 (+113F)
Physical	
MOL	4.31
MOD	2.38
Additional Information	
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day
Compliance	
Safety Listing	cULus
Location Rating	Damp
	Yes
Energy Star	100
Energy Star ES Unique ID	ESID-2318843

•	' '
Compliance	
Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2318843
CEC Status	Non-Compliant
CEC Compliant Substitute	S8561
RoHS Compliant	Yes
SDS Sheet	LED_Lamp





