

Project Name

Location

Prepared By



## SATCO S29596

9.5A19/LED/27K/ND/120V/4PK

### Notes

[www] 03-22-2021 04:50:55

### General

Status	Active
Watts	9.5
Incandescent Equivalent	60
Fluorescent Equivalent	13
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	800
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

### Electrical

Power Factor	0.6
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

### Physical

MOL	4.31
MOD	2.38
Housing Color	White

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
California Compliant Substitute	S8560
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp