

Project Name

Location

Prepared By



SATCO S29597

9.5A19/LED/50K/ND/120V/4PK

Notes

[www] 03-15-2021 00:27:52

General

Status	Discontinued
Substitute	S39597
Watts	9.5
Incandescent Equivalent	60
Fluorescent Equivalent	13
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	85
Lumens	800
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Power Factor	0.6
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	4.31
MOD	2.38

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
California Compliant Substitute	S8563
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp