

## Eaton BR GFCI circuit breaker

**GFTCB115**

**UPC:**786680129766

**Dimensions:**

- **Height:** 1.25 IN
- **Length:** 6 IN
- **Width:** 3.5 IN

**Weight:**.475 LB

**Warranties:** No Data

**Specifications:**

- **Type:** Ground fault personnel protection circuit breakers
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** GFTCB
- **Circuit Protection:** Ground fault circuit interrupter
- **Indicator:** GFI
- **Protection:** 5 mA

**Supporting documents:**

- [Loadcenters and Circuit Breakers](#)
- [Eaton Specification Sheet - GFTCB115](#)

**Certifications:**

- UL 943
- UL 489

**Product compliance:** No Data

