

## Eaton C440 electronic overload relay

C440B1A100SAX

UPC:786685412429

### Dimensions:

- **Height:** 4.13 IN
- **Length:** 5.52 IN
- **Width:** 2.21 IN

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Reset:** Selectable Auto/Manual
- **Frame Size:** 55mm
- **Overload Range:** 20-100A
- **Size:** Separate Mount
- **Special Features:** Standard
- **Trip Type:** Selectable 10A, Class 10 ,20, 30
- **Type:** Electronic overload relay

### Supporting documents:

- [C440 Electronic Overload Relay](#)
- [Eaton's Volume 5-Motor Control and Protection](#)
- [C440B\\_AX 3D Model Xchange](#)
- [C440B\\_AX 2D PDF](#)
- [C440B\\_AX 2D Drawing Xchange](#)
- [C440B\\_AX AutoCAD 2D Footprint \(mm\)](#)
- [C440B\\_AX AutoCAD 2D Footprint](#)
- [C440 NEMA Electronic Overload - Self Powered](#)
- [Eaton Specification Sheet - C440B1A100SAX](#)

### Certifications:

- CSA Certified
- UL Listed



**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.