

Project Name

Location

Prepared By



SATCO S8567

15.5A19/LED/30K/ND/120V/4PK

Notes

[www] 11-02-2020 01:57:08

General

Status	Active
Watts	15.5
Incandescent Equivalent	100
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	90+
Lumens	1490
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
-----------------------	---

Physical

MOL	4.63
MOD	2.38
Housing Color	White

Additional Information

Additional Info	Rough Service; Vibration Service
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp