SATCO NUVO

Project Name

Location Prepared By



Ν	OI	е	s

General		
Status	Active	
Watts	12.5	
Incandescent Equivalent	75	
Volts	120V	
Shape	A19	
Base	Medium	
ANSI Base	E26	
Finish	Frosted White	
CCT (Kelvin)	4000	
Temperature	Cool White	
CRI	90+	
Lumens	1050	
Beam Spread	220	
Dimmable	Non-Dimmable	
Hours Rated	10000	
Lamp Type	Туре А	
Technology	LED	
Electrical		
Power Factor	0.9	
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)	
Physical		
MOL	4.38	

	(1.131)
Physical	
MOL	4.38
MOD	2.38
Housing Color	White

Additional Information		
Rated For Enclosed Fixture	Yes	
Warranty	3 Year Limited	

Compliance	
Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp





