

Project Name

Location

Prepared By



SATCO S8490

15.5A19/LED/40K/ND/120V/4PK

Notes

[www] 01-11-2021 01:30:40

General

Status	Active
Watts	15.5
Incandescent Equivalent	100
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	4000
Temperature	Cool White
CRI	90+
Lumens	1490
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.63
MOD	2.38
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp