

Project Name

Location

Prepared By



## SATCO S8499

12.5A19/LED/30K/ND/120V/4PK

**Notes**

[www] 01-04-2021 03:30:05

**General**

Status	Active
Watts	12.5
Incandescent Equivalent	75
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted
CCT (Kelvin)	3000
Temperature	Warm White
CRI	90+
Lumens	1050
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	10000
Lamp Type	Type A
Technology	LED

**Electrical**

Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

**Physical**

MOL	4.38
MOD	2.38
Housing Color	White

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

**Compliance**

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp