


## NOTES:

1. CAST IRON FLOOR BOX WITH POLYMER UPPER BOX WALL EXTENDING FROM TOP. POLYMER BOX WALL CAN BE SAW-CUT FLUSH TO CONCRETE FLOOR.
2. 140 CU. INCHES MAXIMUM VOLUME 25 CU. INCHES PER INCH OF DEPTH
3. 1" AND 1-1/2" THREADED HUBS PROVIDE SERVICE TO BOX OR FEED THROUGH TO TO OPPOSITE SIDE.
4. FURNISHED COMPLETE WITH:  
 QTY.1 68-HP-CI CAST IRON FLOOR BOX  
 QTY.1 TEMPORARY CONCRETE CAP  
 QTY.2 1-1/2" PLUGS FOR CONDUIT HUBS  
 QTY.2 1" PLUGS FOR CONDUIT HUBS  
 QTY.2 GROUND SCREWS IN BOX  
 QTY.1 GROUND WIRE IN BOX
5. MINIMUM CONCRETE BOX DEPTH:  
 4" FOR FUNITURE FEED SERVICE.  
 4-1/2" FOR FLUSH SERVICE



## CATALOG NO: 68-HP-CI CAST IRON FLOOR BOX

### GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.

### REVISIONS

- |   |                                                                                  |
|---|----------------------------------------------------------------------------------|
| 1 | SEE ERN 2013889 FOR APPROVAL SIGNATURES & RELEASE DATE.<br>PROJECT NO: 5AM400388 |
|---|----------------------------------------------------------------------------------|

### DESCRIPTION:

## 68-HP-CI CAST IRON FLOOR BOX

ORIGINAL PROJECT NO / ( ERN NO )  
UD55819 / ( 2011942 )

SHEET NO:  
1 OF 1

REV. NO:  
1

DRAWING NO:  
WSD-000583

**Thomas & Betts**  
www.tnb.com