



## SINGLE GANG NON-METALLIC CABLE BOXES - BRACKETED

Two-gang with Brackets for Metal or Wood Studs - For Nonmetallic sheathed Cable  
2-3/4 in. Deep, 37.0 Cu. in., 1/2 in. Setback, Bracket, Ground Screw

A77



Catalog #: 2002RAC

### APPLICATIONS

RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires  
Accommodates wiring devices such as switches and receptacles  
Provide excellent protection for wiring system or devices

### PRODUCT FEATURES

RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install  
Single-gang boxes have knockouts that break out quickly and cleanly for faster installation  
Positioning tabs for fast accurate mounting on studs or joists  
N/A

### CSA

CSA Listed

### COMPLIANCES

Boxes are listed for Applications (Electrical Codes), UL Green Book  
Boxes are listed for mechanical properties, including the 2-hour Fire Rating, (building codes) UL Orange Book  
Federal Manufacturer's number 28488

### FIRE RESISTANCE

2-hour fire rating, UL Orange Book

### US PATENTS

4,580,689; 4,666,055

### OTHER PATENTS

Canada 1,237,515; 1,260,599

### GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable  
Color: Yellow

### CONFIGURATION

Cable Knockouts(s): 8  
Bracket Type: Flush  
Bracket Setback: 1/2 in.

### DRAWING DIMENSIONS

Dimension A: 2-3/4 in.  
Dimension C: 3-21/32 in.  
Dimension D: 1/2 in.

### PRODUCT MEASUREMENTS

Depth: 2-3/4 in.  
Cubic Inches (cm3): 37.0 (606.3)  
Wt. Ea. (Lbs.): 0.208  
Product Length (in.): 2.75  
Product Width (in.): 4.69  
Product Height (in.): 6.09

### PACKAGING

Minimum Pack Qty.: 50  
Std. Pkg.: 50  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 27.12  
Ship Carton Length (in.): 24.88  
Ship Carton Width (in.): 11.50  
Ship Carton Height (in.): 15.50

Ctn Weight (Lbs.):	13.56
Pallet Qty:	600
UPC Number:	805035049877
I2of5:	30805035049878