

# DBVR131CGC

Vertical Low Profile IN BOX™ for Retrofit Siding Construction



Low Profile InBox™ for Retrofit Siding Construction (Vertical) with grounding clip

Country of Origin: USA

Weight: 1.536 lbs/each

Height: 7.186"

Width: 4.934"

Material(s): UV-Rated Plastic

NEC Compliance: Meets 2017 NEC Section 406.9 (B) for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Siding Type: 1/4" or 5/16" Lap

Style: Vertical

Trade Size: 1-Gang

## Packaging

Unit: 1 pc

Standard: 4 pcs



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)