SATCO NUVO

Project Name

ocation Prepared By



Made
NOTES

www] 11-29-2020 19:29:51

General	
Status	Active
Watts	36
Fluorescent Equivalent	113
Volts	120V-277V
Ballast Type	Туре В
Shape	Т8
Base	Recessed Double Contact HO/VHO
ANSI Base	R17d
Nominal Length	96
Finish	Frosted
CCT (Kelvin)	6500
Temperature	Daylight
CRI	83
Lumens	5000
Beam Spread	360
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED
Electrical	
Ballasting Requirements	Ballast Bypass

Electrical	
Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60 Hz
Power Factor	0.9
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

Physical	
MOL	93.88
MOD	1

Additional Information	
Installation Notes	No ballast or external driver required; Direct wire 120-277V line voltage; Single ended wiring
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass - Outdoor Sign

Compliance	
Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
NSF Approved	Yes - Approved







