## SATCO NUVO

Project Name

Location

Prepared By



## **SATCO S39390**

18W/LED/HID/5000K/100-277V E26

Notes

[www] 03-22-2021 04:50:5

General	
Status	Active
Watts	18
Incandescent Equivalent	120
Fluorescent Equivalent	32
HID Equivalent	70
Volts	100V-277V
Shape	Corncob
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	2610
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Min Compartment Size	Length: 6 in. Width: 8.5 in. Depth: 6 in.
Ballasting Requirements	Ballast Bypass-Direct wire only 100 277V
Electrical	
Working Voltage	AC 90-305V
Operating Frequency	50/60 Hz
Power Factor	>0.9

Electrical	
Working Voltage	AC 90-305V
Operating Frequency	50/60 Hz
Power Factor	>0.9
Burning Position	Universal
Surge Protection	Built-in surge protection - 2.5KV
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical	
MOL	5.69
MOD	2.38
Lens Finish	Clear
Lens Material	Plastic
Housing Color	White
Weight (lb.)	0.66

Additional Information	
Additional Info	UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Shatter-Proof Type	Shatter resistant materials. Acceptable for use in food prep areas









Compliance	
Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp







