

Project Name

Location

Prepared By



## SATCO S39391

22W/LED/HID/5000K/100-277V E26

### Notes

[www] 03-22-2021 04:50:55

### General

|                         |   |
|-------------------------|---|
| Status                  | Active                                    |
| Watts                   | 22  |
| Incandescent Equivalent | 150                                       |
| Fluorescent Equivalent  | 40  |
| HID Equivalent          | 100                                       |
| Volts                   | 100V-277V                                 |
| Shape                   | Comcob                                    |
| Base                    | Medium                                    |
| ANSI Base               | E26                                       |
| Finish                  | Clear                                     |
| CCT (Kelvin)            | 5000                                      |
| Temperature             | Natural Light                             |
| CRI                     | 80  |
| Lumens                  | 3080                                      |
| Beam Spread             | 300                                       |
| Dimmable                | Non-Dimmable                              |
| Hours Rated             | 50000                                     |
| Lamp Type               | Comcob                                    |
| Technology              | LED                                       |
| Min Compartment Size    | Length: 8.5 in. Width: 6 in. Depth: 6 in. |
| Ballasting Requirements | Ballast Bypass-Direct wire only 100-277V  |

### Electrical

|                       |  |
|-----------------------|--|
| Working Voltage       | AC 90-305V                               |
| Operating Frequency   | 50/60 Hz                                 |
| Power Factor          | >0.9                                     |
| Burning Position      | Universal                                |
| Surge Protection      | Built-in surge protection - 2.5KV        |
| Operating Temperature | -25C (-13F) to a maximum of +45C (+113F) |

### Physical

|               |         |
|---------------|---------|
| MOL           | 5.69    |
| MOD           | 2.38    |
| Lens Finish   | Clear   |
| Lens Material | Plastic |
| Housing Color | White   |
| Weight (lb.)  | 0.68    |

### Additional Information

|                            |   |
|----------------------------|---|
| Additional Info            | UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg) |
| Rated For Enclosed Fixture | Yes   |
| IP Rating                  | IP64  |
| Shatter-Proof Type         | Shatter resistant materials. Acceptable for use in food prep areas  |

Warranty

5 Year Limited - Hi-Pro

| Compliance        |                               |
|-------------------|-------------------------------|
| Safety Listing    | cULus                         |
| Location Rating   | Damp                          |
| Energy Star       | No                            |
| California Status | Lawful for sale in California |
| Nevada Status     | Lawful for sale in Nevada     |
| RoHS Compliant    | Yes                           |
| FCC Compliant     | Yes                           |
| SDS Sheet         | LED_Lamp                      |

