## SATCO NUVO

Project Name

Location

Prepared By



## **SATCO S39394**

54W/LED/HID/5K/100-277V/EX39

Notes

[www] 03-22-2021 04:50:5

General	
Status	Active
Watts	54
Incandescent Equivalent	300
Fluorescent Equivalent	85
HID Equivalent	250
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	7722
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Min Compartment Size	Length: 15.75 in. Width: 8 in.  Depth: 8 in.
Ballasting Requirements	Ballast Bypass-Direct wire only 100 277V
Electrical	
Working Voltage	AC 100-277V
Operating Frequency	50/60 Hz
Power Factor	>0.9
Burning Position	Up or Down Operation Only
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
Physical	
MOL	9.03
MOD	3.34
Lens Finish	Clear
Lens Material	Plastic
Housing Color	White
Weight (lb.)	1.89
Additional Information	
	Approved for totally enclosed
Additional Info	fixtures; Base up or base down operation: For outdoor & indoor

Additional Information	
Additional Info	Approved for totally enclosed fixtures; Base up or base down operation; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Shatter-Proof Type	Shatter resistant materials. Acceptable for use in food prep

For More Information Visit: <a href="https://www.satco.com/">https://www.satco.com/</a>









	areas	
Warranty	5 Year Limited - Hi-Pro	
Compliance		
Safety Listing	cULus	
Location Rating	Damp	
Energy Star	No	
DLC Approved	Yes	
DLC ID	PLXDJHRLRK97	
California Status	Lawful for sale in California	
Nevada Status	Lawful for sale in Nevada	
RoHS Compliant	Yes	
FCC Compliant	Yes	
SDS Sheet	LED_Lamp	







