

Project Name

Location

Prepared By



SATCO S39674

54W/LED/HID/4K/100-277V/EX39

Notes

[www] 03-22-2021 04:50:57

General

Status	Active
Watts	54
Incandescent Equivalent	300
Fluorescent Equivalent	85
HID Equivalent	250
Volts	100V-277V
Shape	Comcob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80
Lumens	7560
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Comcob
Technology	LED
Min Compartment Size	Length: 15.75 in. Width: 8 in. Depth: 8 in.
Ballasting Requirements	Ballast Bypass-Direct wire only 100-277V

Electrical

Working Voltage	AC 100-277V
Operating Frequency	50/60 Hz
Power Factor	>0.9
Burning Position	Up or Down Operation Only
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	9.03
MOD	3.34
Lens Finish	Clear
Lens Material	Plastic
Housing Color	White
Weight (lb.)	1.89

Additional Information

Additional Info	Approved for totally enclosed fixtures; Base up or base down operation; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Shatter-Proof Type	Shatter resistant materials. Acceptable for use in food prep

	areas
Warranty	5 Year Limited - Hi-Pro
Compliance	
Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLUH2DVRZ8XC
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp