
MEDIUM BASE LAMPHOLDER

3352F | [Pass & Seymour](#)



FEATURES & BENEFITS

Medium base, porcelain, keyless, screw terminals, short base. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Medium Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CSA Standard: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39111803
UR: No

DIMENSIONS

Diameter (Metric): 1.38"
Height (US): 2.00"

TECHNICAL INFORMATION

Volts: 250V

Volts (AC): 250

Watts: 660

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No