

## Eaton definite purpose contactor

C25ENF440T

UPC:782113536613

### Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.38 IN
- **Width:** 2.68 IN

**Weight:**2.3 LB

**Notes:**Resitive Load rating per pole

### Warranties:

- 1 year

### Specifications:

- **Connection:** Quick
- **Amperage Rating:** 40A
- **Coil:** 24 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Four-pole
- **Resistive Load:** 50A
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [C25ENF4 AutoCAD 2D Footprint \(mm\)](#)
- [C25ENF4 2D Drawing Xchange](#)
- [C25ENF4 3D Model Xchange](#)
- [C25ENF4 2D PDF](#)
- [C25ENF4 3D Inventor](#)
- [C25ENF4 AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - C25ENF440T](#)

### Certifications:



- UL Recognized
- CSA Certified

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.