Eaton E50 NEMA heavy duty plug-in limit switch

E50SAL

UPC:782113775364

Dimensions:

Height: 1.73 INLength: 3.14 INWidth: 1.54 IN

Warranties:

• 1 year

Specifications:

• Contact Rating: 10A at 12 Vac, 1A at 125 Vdc

• Contact Configuration: 1NO-1NC

• Enclosure Material: Die cast zinc

• Environmental Rating: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67

• Led Indicators: LED indicator

• Light Unit Voltage: 24-120 Vac/dc

Maximum Ac Current: 10AMaximum Dc Current: 1A

• Number Of Poles: Single-pole

• Operating Temperature: -40° to 250°F (-40° to

121°C)

• Series: E50 Heavy Duty Plug In

Supporting documents:

• Eatons Volume 8-Sensing Solutions

• Eaton Specification Sheet - E50SAL

Certifications:

CSA Certified

UL Recognized

Product compliance: No Data

